

## CEL-MET<sup>®</sup> CPP 30 $\mu$ m METALLIZED CAST POLYPROPYLENE FILM Typical Values

Metal One Side, Heat Sealable Other Side

High barrier metallized cast polypropylene. A highly reflective low slip surface in a differentiated copolymer polypropylene. Provides good machine-ability and side weld seals. Suitable for medical and gel sensitive laminations. *Available 0.80 mil – 2.0 mil*

Properties	Typical Value		Units	Test Method
<b>Yield</b>	36,40		m <sup>2</sup> /kg	
<b>Thickness</b>	1,20 30		Mil $\mu$ m	
<b>Tensile Strength</b>	47,0 20,0	MD TD	N/mm <sup>2</sup>	ASTM D882
<b>Minimum Heat Seal Strength</b>	5,12		N/25mm	ASTM F 88-85 0.5 sec, 60 psi, 230° F
<b>Ultimate Seal Strength</b>	25,0		N/25mm	ASTM F 88-85 0.5 sec, 60 psi, 252° F
<b>Elongation</b>	400 500	MD TD	%	ASTM D882
<b>Optical Density</b>	2.0		Macbeth	CMP OD-1
<b>Light Transmission</b>	< 1.0		%	
<b>Coefficient of Friction</b>	0,18	Kinetic	-	ASTM D1894
<b>WVTR</b>	0,62		g/m <sup>2</sup> /24 hr.	ASTM E-398 (100° F, 90% RH)
<b>OTR</b>	46-78		cc/m <sup>2</sup> /24 hr.	ASTM D-3985 (73.4° F, 50% RH)
<b>Metal Adhesion</b>	3,0		N/25mm	CMP MA-1

The CPP side is in compliance with the regulation FDA 21 CFR 177.1520 (3.1).

The information and opinions herein are believed to be true and accurate and presented without guarantee or responsibility on our part. No recommendation for use of our product is intended as a patent infringement. No warranty of any kind with respect to patents held by others is implied or intended. Celplast does not guarantee the Corona Treatment on metallized CPP films. We suggest applying primer or re-treating in line or consult your ink and adhesive supplier to achieve optimum results.